

Specifications:

Resonant Frequency (Hz)	4100 ± 500
Operating Voltage (Vdc)	3 ~ 15
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	5 at Rated Voltage
Sound Pressure Level Min. (dB)	83 at 10cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +90
Storage Temperature (°C)	-30 ~ +100
Housing	ABS 777D UL94HB plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Condition by Wave Soldering (°C)	245 ± 5° for 3 ± 0.5 seconds
Condition by Hand Soldering (°C)	350 ± 20° within 5 seconds
Weight (Grams)	.8
Options	For other options contact factory

RoHS Compliant**Dimensions:** (units: mm)