




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			G1	REDRAWN PER ECO-12-019442	06NOV12	KH	DR

- 1 MATERIAL: COPPER PER ASTM B152
INSULATION: PVC
- 2 FINISH: TIN PLATED PER ASTM B545
INSULATION: COLOR: BLUE
- 3 STAMP AMP 16-14* APPROX AS SHOWN
- 4 WIRE INSULATION DIAMETER
4.95[.195] MAX

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 343°C [649°F] VOLTAGE RATING: N/A CIRCULAR MILL AREA: 1.04-2.62mm²[2,050-5,180] SOLID OR STRANDED
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± 0.20[.008]
	4 PLC ± -
	ANGLES ± -
MATERIAL	FINISH
1	2

DWN KIRAN HOLAL	06NOV12	TE Connectivity			
CHK ROHDE DANIEL	06NOV12				
APVD ROHDE DANIEL	06NOV12	NAME TERMINAL PLASTI GRIP RECTANGULAR TONGUE(SLOTTED), WIRE SIZE 16-14			
PRODUCT SPEC —		SIZE A3	CAGE CODE 00779	DRAWING NO C-160213	RESTRICTED TO —
APPLICATION SPEC —		SCALE 8:1		SHEET 1 OF 1	REV G1
WEIGHT —		CUSTOMER DRAWING			