


**Panel Mount Indicator, Non-Relampable
LED Technology
Mounting Hole, Ø 0.500"**



All dimensions are in inches



RoHS
COMPLIANT

Recommended panel thickness: 0.030" to 0.090"

6" leads with 1/2" strip are standard

Storage temperature	T _{STG} : -25°C - +80°C
Ambient temperature	T _A : -20°C - +60°C
Voltage tolerance	V _{OP} : ±10%

[illegible]

Body Material:	Nylon, white
Lens Material:	Polycarbonate
Bezel Material:	Stainless steel
Wire Gauge:	18 AWG
Wire Strip:	1/2"
Anode(+):	Red lead

Certifications: Most Wamco indicators carry Agency approvals. Please contact Wamco for the latest Agency information regarding the specific product series and voltage required.

Options: Additional options and lens styles available. Please contact Wamco for more information.

Drawn	SC	03/01/10	Panel Mount Indicators LED	Datasheet: WL-1091MX-XXX Series	Rev: 2
Checked	EB	03/01/10			
Approved	EB	03/02/10			