

0314.500 - 314 Series



Series: 314

Questions? [Contact Littelfuse Support](#)

 [Fuse 314 and 324 Datasheet](#)

The 3AB Fast-Acting Fuse with ceramic body construction permits higher interrupting ratings and voltage ratings. Ideal for applications where high current loads are expected.

Features:

- In accordance with UL Standard 248-14
- Available in cartridge and axial lead format and with various forming dimensions
- RoHS compliant and Lead-free

 [Check Stock](#)

 [Order Samples](#)

Electrical Characteristics	Technical Resources	Environmental Info
Property (Mouseover for details)		
		Value
Ampere Rating (A)		0.5
Body		Ceramic Body
Nominal Melting I ² T (A ² sec)		0.639
Interrupting Rating		10000A@125VDC
Marking Code		VX
Moisture Sensitivity Level		Contact Littelfuse
Nominal Cold Resistance (Ohms)		0.504
Opening		Fast-Acting (F)
Min Operating Temp °C		-55
Max Operating Temp (°C)		125
Package Size		3AB/3AG (6.3x32mm)
VAC (V)		250
VDC (V)		125

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email

Submit

For more details about how we use your information, check our [Privacy Statement](#).



 [Mobile Site](#)

About Littelfuse

- [About Littelfuse](#)
- [Conflict Free Statement](#)
- [History](#)
- [Investor Relations](#)
- [Legal](#)
- [Press Room](#)
- [Privacy Statement](#)
- [Supply Chain Transparency](#)
- [Website Feedback](#)

Explore Littelfuse

- [Capabilities Brochures](#)
- [Careers](#)
- [Check Distributor Stock](#)
- [Competitor Cross Reference](#)
- [Industries](#)
- [Order Samples](#)
- [Products](#)
- [Services](#)

Technical Resources

- [Application Designs](#)
- [Education](#)
- [FAQs](#)
- [iDesign™](#)
- [Littelfuse University](#)
- [Product Catalogs](#)
- [Quality Documents](#)
- [Technical Documents](#)

Feedback