



Common mode choke

Order code	TCK-087
Inductance	Pin 1-2: 224 $\mu\text{H} \pm 35\%$ (at 100 kHz / 100 mV) Pin 3-4: 224 $\mu\text{H} \pm 35\%$ (at 100 kHz / 100 mV)
Rated current	15.4 A max.
DCR	Pin 1-2: 4.16 m Ω Pin 3-4: 4.16 m Ω
Rated voltage	500 VDC
Operating temperature	-40 to +105°C

Impedance curve



Dimensions [mm]

A	16.6 ± 0.4
B	16.4 ± 0.4
C	12.5 max.
D	5.0 ± 1.0
E	14.1 ± 0.5
F	6.1 ± 0.5
G	$\varnothing 1.6$ max.