

Type CGO Ultra Low ESR Screw Terminal Aluminum Electrolytic

Extremely Low ESR, Low Voltage, Screw Terminal Capacitors



Type CGO low voltage, low ESR, screw terminal aluminum electrolytic capacitors have extremely low ESR and are suitable for output filtering in switch mode power supply applications.

Highlights

- Extremely low ESR
- Low voltage
- Screw Terminal
- 35 mm diameter

[RoHS Compliant](#)

Specifications

Capacitance Range:	2,800 to 45,000 µF
Voltage Range:	5 to 55 WVdc
Capacitance Tolerance:	±20%
Operating Temperature:	−40 to +85 °C
Ripple Current Multipliers:	The maximum ripple current at 85 °C and 20 kHz for CGO capacitors is shown in the standard Ratings Tables. Maximum ripple current may be adjusted by the multipliers in the tables below.

Ambient Temperature / Ripple Multiplier

+35 °C	+45 °C	+55 °C	+65 °C	+75 °C	+85 °C
2.15	1.93	1.73	1.50	1.30	1.00

Rated Voltage	Frequency / Ripple Multiplier				
	120 Hz	400 Hz	1000 Hz	2500 Hz	10 kHz
5 to 55	.84	.85	.86	.87	.95

DC Leakage Current: $I \leq 1.5 \sqrt{CV}$ after 5 minutes
C = Capacitance in µF
V = Rated Voltage
I = Leakage current in µA

QA Stability Test: Apply WVdc for 1000 h @ 85 °C
Capacitance change ≤15% from initial limits
DC leakage current meets initial limits
ESR ≤175% of initial measured value

[Click here to see: Hardware & Mounting Options](#)

[Click here to see: Mechanical Details](#)

Type CGO Ultra Low ESR Screw Terminal Aluminum Electrolytic

Ratings

Cap (μF)	Catalog Part Number	Typical ESR		Max Ripple	Dia. (In.)	Length (In.)
		120 Hz (Ω)	20 kHz (Ω)	20 kHz (A) RMS		
5 WVdc (6 Vdc Surge)						
18000	CGO183M005L	0.016	0.009	9.8	1.375	2.125
7.5 WVdc (9 Vdc Surge)						
15000	CGO153M7R5L	.0158	0.010	9.4	1.375	2.125
21000	CGO213M7R5L	0.013	0.008	10.9	1.375	2.625
27000	CGO273M7R5L	0.011	0.007	12.7	1.375	3.125
33000	CGO333M7R5L	0.009	0.006	14.2	1.375	3.625
39000	CGO393M7R5L	0.009	0.006	15.5	1.375	4.125
45000	CGO453M7R5L	0.008	0.005	17.5	1.375	4.625
10 WVdc (12 Vdc Surge)						
14000	CGO143M010L	0.018	0.010	9.3	1.375	2.125
19000	CGO193M010L	0.013	0.008	10.9	1.375	2.625
16 WVdc (18 Vdc Surge)						
10000	CGO103M016L	.0167	0.010	9.3	1.375	2.125
14000	CGO143M016L	0.008	0.006	10.9	1.375	2.625
18000	CGO183M016L	0.011	0.007	12.6	1.375	3.125
22000	CGO223M016L	0.010	0.006	14.2	1.375	3.625
20 WVdc (22 Vdc Surge)						
12000	CGO123M020L	.0142	0.009	10.8	1.375	2.625
16000	CGO163M020L	0.012	0.007	12.6	1.375	3.125
20000	CGO203M020L	0.010	0.007	14.1	1.375	3.625
22000	CGO223M020L	0.009	0.006	15.4	1.375	4.125
27000	CGO273M020L	0.008	0.005	17.4	1.375	4.625
34000	CGO343M020L	0.007	0.005	19.6	1.375	5.625

Cap Cap (μF)	Catalog Part Number	Typical ESR		Max Ripple	Dia. (In.)	Length (In.)
		120 Hz (Ω)	20 kHz (Ω)	20 kHz (A) RMS		
28 WVdc (32 Vdc Surge)						
6300	CGO632M028L	0.021	0.012	8.3	1.375	2.125
8800	CGO882M028L	0.017	0.010	9.9	1.375	2.625
8900	CGO892M028L	0.017	0.010	10.1	1.375	2.625
14000	CGO143M028L	0.012	0.008	13.1	1.375	3.625
35 WVdc (40 Vdc Surge)						
4,500	CGO452M035L	0.024	0.012	8.2	1.375	2.125
6300	CGO632M035L	0.019	0.010	9.8	1.375	2.625
8100	CGO812M035L	0.015	0.009	11.5	1.375	3.125
10000	CGO103M035L	0.013	0.008	13.0	1.375	3.625
14000	CGO143M035L	0.010	0.006	16.1	1.375	4.625
45 WVdc (50 Vdc Surge)						
3800	CGO382M045L	0.032	0.018	8.1	1.375	2.125
4600	CGO462M045L	0.024	0.013	9.7	1.375	2.625
10000	CGO103M045L	0.022	0.013	15.6	1.375	4.625
55 WVdc (64 Vdc Surge)						
2800	CGO282M055L	.0302	0.015	7.5	1.375	2.125
3900	CGO392M055L	0.023	0.012	9.0	1.375	2.625
5000	CGO502M055L	0.019	0.010	10.6	1.375	3.125
10000	CGO103M055L	0.011	0.006	17.2	1.375	5.625

Notice and Disclaimer: All product drawings, descriptions, specifications, statements, information and data (collectively, the “Information”) in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements (“Cornell Dubilier”) has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.