



Climate control accessories Page 471 Software & services Page 511

Protection rating:

UL/cUL recognized, CSA
UL Type 12/IP 54
UL file #: SA8250

Configuration:

- Fully wired ready for connection
- Includes drilling template and assembly parts


- With nano-coated condenser and integrated condensate evaporator

Note:

Air conditioners with comfort controller may be integrated into a monitoring system with an optional interface card 3124.200 (RS 232, RS 485, RS 422 and PLC interface). See page 477.

Additional parts needed:

For installation in the door, the use of a door alignment roller (4538.000) is recommended, see page 618.



Useful cooling capacity: 16841 BTU (4933 W)

Part No. with comfort controller, RAL 7035 (light grey)	3332.540
Part No. with comfort controller, Type 304 stainless steel	3332.640
Voltage V, Hz	400, 50/460, 60, 3~
Dimensions inches (mm)	62 x 20 x 13 (1580 x 500 x 340)
Useful cooling capacity Q_k BTU (W)	T _i 131 T _a 131 16841 (4933)
Useful cooling capacity Q_k to DIN 3168 BTU (W)	T _i 95 T _a 95 13661/15027 (4000/4400) T _i 95 T _a 122 10485/12192 (3070/3570)
Rated current maximum	4.2 A/4.2 A
Starting current	9.2 A/11.0 A
Pre-fuse T	Motor circuit breaker 10.0 A/10.0 A
Power consumption Pel to DIN 3168	T _i 95 T _a 95 1710 W/2110 W T _i 95 T _a 122 1980 W/2450 W
Cooling coefficient $j = Q_k/Pel$	T _i 95 T _a 95 2.3
Refrigerant	R134a, 105.8 oz (3000 g)
Maximum allowable operating pressure	406 psi (28 bar)
Temperature and setting range	Comfort controller - +68 to +131° F (+20 to +55° C)
Environmental ratings	UL Type 12 (IP 54)
Duty cycle	100%
Type of connection	Plug-in terminal strip
Weight lb (kg)	200.6 (91)
Air displacement of fans	External circuit 1177 cfm (2000 m ³ /h) Internal circuit 883 cfm (1500 m ³ /h)
Temperature control	Comfort controller (factory setting 95° F (+35° C))
Accessories	PU
Filter mats	3
Metal filters	1
Door-operated switch	1
Master/slave cable for comfort controller	1
RiDiag II including cables for comfort controller	1
Interface card for comfort controller	1
Condensate hose	1

Special voltages available on request. We reserve the right to make technical modifications.