

[HOME](#)[CHECK ORDER](#)[ABOUT US](#)[CONTACT US](#)[REQUEST CATALOG](#)**PRODUCT FAMILIES**

[Pin Headers and Sockets](#)
[Clips and Insulators](#)
[Banana Plugs and Jacks](#)
[Grabbers, Probes and Spade Terminals](#)
[Plunger Clips](#)
[Test Probes](#)
[Spade Terminals](#)
[Test Leads and Patch Cords](#)
[Coaxial Cable Assemblies](#)
[DMM Kits](#)

ISO 9001:2000

Plunger Clips

Plunger Clip[CHECK INVENTORY](#)

Model # BU-00201-*/BU-00202-*/BU-00203-*

- Material: Cap & Body: glass filled nylon; Spring: stainless steel; Contact: beryllium copper; insulated to a single contact point
- Length: 1.75" (44mm) (BU-00201-*); 2.50" (63mm) (BU-00202-*); 3.50" (88mm) (BU-00203-*)
- *Std. Colors: -0 Black, -2 Red
- Rating: 1000 Volts, 10 Amps

Safety Plunger Clip Adapter[CHECK INVENTORY](#)

Model # BU-00207-*

- Material: Cap & Body: nylon; Spring: stainless steel; Contact: beryllium copper
- Length: 2.23" (56.64mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 1000 Volts, 15 Amps

Mini-Micro Plunger Clip



CHECK INVENTORY

Model # BU-00208-*

- Material: Cap & Body: tough, durable nylon; Spring: stainless steel compression coil; Contact: gold-plated beryllium copper
- Length: 1.75" (44mm)
- *Std Colors: -0 Black, -2 Red
- Rating: 600 Volts, 3 Amps

Right Angle Insulated Plunger Hook Clip



CHECK INVENTORY

Model # BU-20431-*

- Compatible with all shrouded, unshrouded, or retractable 0.16" (4mm) banana plugs
- Material: Housing: nylon. Contact: nickel-plated beryllium copper
- Length: 4.60" (116.84mm); the hook extends 0.41" (10mm) when fully depressed
- *Std Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000V, 15 Amps, IEC 1010 Compliant

Right Angle Insulated Plunger Clamp Clip


[CHECK INVENTORY](#)

Model # BU-20432-*/BU-20433-*

- Compatible with all shrouded, unshrouded, or retractable 0.16" (4mm) banana plugs
- Material: Housing: nylon. Contact: nickel-plated beryllium copper
- Length: 5.50" (139.7mm) (BU-20432-*); 7.50" (190.5mm) (BU-20433-*)
- *Std Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000V, 1 Amps, IEC 1010 Compliant

Right Angle Insulated Plunger Jaw Clip


[CHECK INVENTORY](#)

Model # BU-20434-*

- Compatible with all shrouded, unshrouded, or retractable 0.16" (4mm) banana plugs
- Material: Housing: nylon. Contact: nickel-plated steel
- Length: 5.26" (133.6mm); the steel jaws extend 0.48" (12mm) and open to 1" (25mm)
- *Std Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000V, 15 Amps, IEC 1010 Compliant

TOOL
SEARCH TOOLS

MUELLER OR DISTRIBUTOR
 STOCK SEARCH

TOOL
CROSS COMPETITOR PART #

TOOL
**MeterMate® DMM ACCESSORY
SELECTOR**

TOOL
**BUILD A PCB HEADER OR
SOCKET**

OVER 10,000 IN STOCK!

© 2008 Mueller Electric Company, Inc.

[Home](#) | [Products](#) | [Check Order Status](#) | [About Us](#) | [Contact Us](#) | [Request a Catalog](#) | [Site Map](#)