




REV.	DATE	DESCRIPTION
NC	08/08/02	INITIAL RELEASE

INTERNAL NOTE:
STAKE IN 4 PLACES
EQUALLY SPACED 90° APART



8				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	APPROVALS	DATE	Amphenol – Connex CONNECTOR CORPORATION					
7					DRAWN	G.R.S.					08/08/02	
6					CHECKED			TITLE SMA SEMI–RIGID PLUG/ CONTACT IN BODY (FOR .085”, .086” CABLE)				
5					ISSUED							
4	CONTACT PIN	BER. COPPER	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .XXX = ± 0.005” .XX = ± 0.010” .X = ± 0.020”			SIZE	FSCM NO.	DWG. NO.	REV.		
3	INSULATOR	TEFLON	NATURAL				A	99001	132294–11.DWG	NC		
2	BODY	BRASS	GOLD									
1	NUT	S/S	PASSIV. S/S									
	DESCRIPTION	MATERIAL	FINISH	DO NOT SCALE DRAWING			SCALE	NA	PART NO.	132294–11	SHEET	1 OF 1