

**NO MERCURY ADDED**


Description	: Mercury Free Extra Heavy Duty Battery, D Size
Chemical System	: Zinc Chloride
Nominal Voltage	: 1.5 Volts
Nominal Dimensions	: $\varnothing 34.2$ mm x 61.5 mm
Terminals	: Protruded positive(+) and flat negative(-) contacts
Jacket	: Metal jacket with PVC tube insulation
Applications	: All electronic devices, e.g. transistor radios, cassette recorders, toys, alarm clocks, portable fans, portable hand-tools.
Warranty Period	: 24 months
Average Weight	: 95g

**Cross References:**

GP	JIS	IEC	Eveready
13G	R20P	R20P	1250

**Typical Service Life:**

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
3.9 Ohms	1 Hr/ Day	0.9V	15 Hrs



Model No.: **GP13G**

