

Mandatory sign - US-PML-M100 (D50) - 1014176

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Mandatory sign, Card, blue, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD: Blank, Mounting type: Adhesive, Diameter: 50 mm, Lettering field: d: 50 mm

Product Features

- ✓ UniSheet - stick-on mandatory signs, color preprinted, without symbol
- ✓ Suitable for indoor and outdoor use
- ✓ The mandatory signs conform to the ISO 7010 international standard
- ✓ Highly flexible, plasticized PVC labels which are ideal for uneven surfaces

Key commercial data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	6.0 GRM
Custom tariff number	39203000
Country of origin	Germany

Technical data

Dimensions

Width (a)	50 mm
Diameter	50.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (assembly)	> 8 °C
Recommended storage conditions	4 - 40°C Storage in a cool and dark place in the original packaging is recommended.

General

Color	blue
Design	Round
Components	Silicone-free

Mandatory sign - US-PML-M100 (D50) - 1014176

Technical data

General

Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	Blank
Number of individual labels	4
Adhesive	Acrylic
Device	5146464 THERMOMARK CARD
	5146481 THERMOMARK CARD PLUS
Ink ribbon	1014402 TM-RIBBON 110-TC/TR WH
	5146451 THERMOMARK CARD-US-MAG1
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Foil strength	50 µm

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27371301
eCl@ss 5.1	27371301
eCl@ss 6.0	27371301
eCl@ss 7.0	27371301
eCl@ss 8.0	27371301

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498

Mandatory sign - US-PML-M100 (D50) - 1014176

Classifications

ETIM

ETIM 5.0	EC000761
----------	----------

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212107

Accessories

Accessories

Ink ribbon

Ink ribbon - TM-RIBBON 110-TC/TR WH - 1014402



Ink ribbon, Length: 240000 mm, Color: white

Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards