



Sample photo

Order symbol: CAB P 604023
Product nbr: 8104306
Description: Polyester cabinet
Remarks: Grey door

EAN: 6418074050038
El. number:
Finland: 3424139
Denmark: 8212018031
Sweden: 2539823
Norway:

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with transport and plastic key.

Dimensions:		Length	Width	Height	Rating:
mm:		615	415	230	Ingress Protection (EN 60529): IP 66
inch:		24.2	16.3	9.1	Impact Resistance (EN 62262): IK 10
Materials:					Electrical insulation: Totally insulated
Material:		Polyester			UV resistance: UL 508
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		Polyurethane			UL Type: UL TYPE 3, 3R, 3S, 4, 4X, 12, 13
Temperatures:					Certificates:
Short term:		-50 ... 160 °C			Gost R
Continuous:		-40 ... 80 °C			
Short term:		-60 ... 320 °F			
Continuous:		-40 ... 176 °F			
Accessories:					
MP 6040		Mounting plate			
MPX 6040		Mounting Plate			
MPP 6040		Mounting Plate			
MF 6040		Mounting Frame with DIN-rails			
FP 6040-3x18		Front Plate with DIN openings			
FP 6040-D		Swing door/Front plate			
MB CAB		Swing door kit			

CAB P 615x415x230

