

RJ45 socket insert - VS-08-BU-RJ45/KA - 1689077

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



RJ45 socket insert, modular (Keystone), CAT3, 8-pos., shielded, with cable connection (IDC)



Ethernet

Key commercial data

Packing unit	1 1
Minimum order quantity	5 1
Weight per Piece (excluding packing)	19.0 GRM
Custom tariff number	85366990
Country of origin	China

Technical data

General

Pollution degree	2
Surge voltage category	II
Insertion/withdrawal cycles	≥ 250
Conductor cross section	0.13 mm² ... 0.2 mm²
Connection cross section AWG	26 ... 24

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Degree of protection	IP20

Material data

Inflammability class according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	Polyester GF

RJ45 socket insert - VS-08-BU-RJ45/KA - 1689077

Technical data

Electrical characteristics

Rated voltage (III/3)	125 V
Rated current	1.5 A

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309

ETIM


ETIM 2.0	EC000438
ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC


UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Drawings

Schematic diagram



Dimensioned drawing



RJ45 socket insert, keystone

