

High Resolution Milliohm Meter

Benchtop meter provides resolution down to 0.01m
Using 4-wire Kelvin clip test leads

Features:

- 7 ranges for wide low resistance measurements
- High resolution to 0.01m
- 1999 count display with 0.8" digits
- Automatic zero
- Built-in comparator for Hi/Lo/Go resistance testing or selection
- 5V test voltage
- One year warranty
- Complete with 4-wire cables with Kelvin clip connectors and power cord



Specifications	Range	Resolution	Current	Accuracy (%rdg)
Resistance	20m	0.01m	1A	±(0.2% + 6d)
	200m	0.1m	1A	±(0.2% + 4d)
	2	0.001	100mA	±(0.2% + 4d)
	20	0.01	10mA	±(0.2% + 4d)
	200	0.1	1mA	±(0.2% + 4d)
	2k	0.001k	100μA	±(0.2% + 4d)
	20k	0.1k	10μA	±(0.2% + 4d)
Power	110VAC, 60Hz or 220VAC 50Hz			
Dimensions/Weight	11 x 8.3 x 3.5" (280 x 210 x 90mm)/ 4.85lb (2.2kg)			

Ordering Information:

380560.....Precision Milliohm Meter, 110VAC
380560-NIST380560 with Calibration Traceable to NIST
380562.....Precision Milliohm Meter, 220VAC
380562-NIST380562 with Calibration Traceable to NIST
380465.....Spare Kelvin Clip Test Lead Set



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[380560](#)