



(1.27 mm) .050"

FFSD-20-S-10.00-01-N



FFSD-10-D-02.00-01-N

FFSD SERIES

TIGER EYE™ FLAT IDC WIRE CABLES

Mates with:

 FTS, FTSH, EHF,
SHF, ESHF

SPECIFICATIONS

 For complete specifications
see www.samtec.com?FFSD
Insulator Material:

PBT

Contact:

BeCu

Plating:

 10 μ" (0.25 μm) Au over 50 μ"
(1.27 μm) Ni on contact area;
Sn over 50 μ" (1.27 μm) Ni
on balance

Wire:

30 AWG

Current Rating (FFSD/FTSH):

 2.3 A per pin
(2 pins powered)

Operating Temp Range:

-40 °C to +105 °C

Lead Size Accepted:

(0.41 mm) .016" SQ

Insertion Depth:

 (2.64 mm) .104" to
(3.17 mm) .125"



RoHS Compliant:

Yes


RECOGNITIONS

 For complete scope of
recognitions see
www.samtec.com/quality


FILE NO. E111594


ALSO AVAILABLE
(MOQ Required)

- Other sizes



Note: This Series is non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.