







PCB LAYOUT - COMPONENT VIEW



TECHNICAL CHARACTERISTICS

INSULATOR: PBT
FLAMMABILITY RATING: UL94-V0
COLOR: BLACK
CONTACT MATERIAL: PHOSPHOR BRONZE
CONTACT TYPE: STAMPED
CONTACT PLATING: GOLD
SHIELDING: BRONZE NI PLATED
QUALITY CLASS: 500 MATING CYCLES

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 TO 85°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 1.5A
WORKING VOLTAGE: 120VAC
INSULATOR RESISTANCE: >1000 MΩ
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VAC/MIN
CONTACT RESISTANCE: 20 mΩ MAX

STANDARD
UL CERTIFIED: E324776

SOLDERING:
JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING
TRAY

RoHS Compliant				PROJECTION: 	TOLERANCES UNLESS OTHERWISE SPECIFIED 0~10 ±0.1 10~20 ±0.15 20~30 ±0.2		DESCRIPTION: SHIELDED 3.05mm FRONT GROUNDING POST 8P8C MODULAR JACK TAB DOWN WERI PART NO: 615 008 140 121	SIZE A4
G	F	E	D					
		03-JAN-14	UL & TEMP UPDATE	QL				
		20-AUG-13	DIM UPDATE	QL				
		05-JUL-12	DIM	GG				
		06-OCT-09	UL STANDARD	JP				
		06-NOV-07	PDF	EC				
REV	DATE	FILE	BY					