


KEMET Part Number: HT06CB104KN
(HT06CB104K, HT06CW104KN)



HTHP LDD Indust X7R HT200C, Ceramic, 200C, 0.1 uF, 10%, 100 V, X7R, Commercial, High Temperature, Lead Spacing = 5.08mm



Dimensions	
L	7.62mm MAX
H	7.62mm MAX
T	3.81mm MAX
S	5.08mm +/-0.76mm
LL	31.75mm MIN
F	0.635mm NOM

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	1

General Information	
Supplier:	KEMET
Series:	HTHP LDD Indust X7R HT200C
Style:	Radial
Description:	Commercial, High Temperature
Features:	Commercial
RoHS:	Yes
Termination:	Nickel
Failure Rate:	N/A

Specifications	
Capacitance:	0.1 uF
Capacitance Tolerance:	10%
Voltage DC:	100 VDC
Dielectric Withstanding Voltage:	250 V
Temperature Range:	-55/+200C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Insulation Resistance:	10 GOhms