


OA172SAP XC Series



AC FAN - Salt Fog Rated
172x150x55mm (6.7"x 5.9"x 2.2")



Frame	Diecast Aluminum	Environmental Protection SALT FOG RATED Operating Temperature -20C ~ +70C Life Expectancy >40,000 hours (L10, 40C) m2	Static Pressure ("H2O)
-------	------------------	---	--

Model Number	OA172SAP-11-1TBXC (SF)	OA172SAP-22-1TBXC (SF)
Part Number	230385562	230685562
Nominal Voltage	115 VAC	230 VAC
Voltage Range	103 ~ 126 VAC	207 ~ 253 VAC
Rated Current	0.34 A	0.17 A
Locked Current	0.76 A	0.38 A
Rated Power	38 W	38 W
Rated Speed (RPM)	3400	3400
Airflow (CFM)	293	293
Noise Level (dB)	60	60
Max. Static Pressure (" H ₂ O)	0.90	0.90