

Type 1 Mild Steel Junction Box *CS Series*

Screw Cover and without Knockouts



Application

- Designed for general purpose indoor commercial use as a junction, pull or switch box.

Standards


- UL-50 Type 1
- CSA Type 1
- Complies with
 - NEMA Type 1
 - IEC 60529, IP20

Construction

- Formed and spot welded from 16, 14 or 12 gauge steel depending on size.
- Flat steel covers fastened with plated steel screws.
- Keyhole slots permit cover to be lifted off without removing screws entirely.
- Through holes in back for wall mounting.
- Grounding location embossed in body.

Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.



Part No.	Overall Dimensions			Mtg. Centers					Ship Wt. lbs.
	A	B	C	D	E	F	G	H	
CS443	4.00	4.00	3.00	2.00	3.00	0.88	0.50	0.28	2
CS663	6.00	6.00	3.00	3.00	5.00	1.50	0.50	0.28	3

Part No.	Overall Dimensions			Mtg. Centers					Ship Wt.
	A	B	C	D	E	F	G	H	lbs.
CS863	8.00	6.00	3.00	5.00	5.00	1.50	0.50	0.28	3
CS16143	16.00	14.00	3.00	13.00	13.00	1.50	0.50	0.28	12
CS18143	18.00	14.00	3.00	15.00	13.00	1.50	0.50	0.28	13
CS20143	20.00	14.00	3.00	17.00	13.00	1.50	0.50	0.28	13
CS444	4.00	4.00	4.00	2.00	3.00	0.88	0.50	0.28	2
CS644	6.00	4.00	4.00	3.00	3.00	1.50	0.50	0.28	3
CS664	6.00	6.00	4.00	3.00	5.00	1.50	0.50	0.28	3
CS864	8.00	6.00	4.00	5.00	5.00	1.50	0.50	0.28	5
CS884	8.00	8.00	4.00	5.00	7.00	1.50	0.50	0.28	5
CS1084	10.00	8.00	4.00	7.00	7.00	1.50	0.50	0.28	6
CS10104	10.00	10.00	4.00	7.00	9.00	1.50	0.50	0.28	6
CS1284	12.00	8.00	4.00	9.00	7.00	1.50	0.50	0.28	7
CS12104	12.00	10.00	4.00	9.00	9.00	1.50	0.50	0.28	8
CS12124	12.00	12.00	4.00	9.00	11.00	1.50	0.50	0.28	9
CS16124	16.00	12.00	4.00	13.00	11.00	1.50	0.50	0.28	12
CS18124	18.00	12.00	4.00	15.00	11.00	1.50	0.50	0.28	12
CS18184	18.00	18.00	4.00	15.00	17.00	1.50	0.50	0.28	16
CS24244	24.00	24.00	4.00	21.00	23.00	1.50	0.50	0.28	33
CS666	6.00	6.00	6.00	3.00	5.00	1.50	0.50	0.28	4
CS886	8.00	8.00	6.00	5.00	7.00	1.50	0.50	0.28	6
CS1086	10.00	8.00	6.00	7.00	7.00	1.50	0.50	0.28	7
CS10106	10.00	10.00	6.00	7.00	9.00	1.50	0.50	0.28	8
CS12106	12.00	10.00	6.00	9.00	9.00	1.50	0.50	0.28	8
CS12126	12.00	12.00	6.00	9.00	11.00	1.50	0.50	0.28	9
CS16126	16.00	12.00	6.00	13.00	11.00	1.50	0.50	0.28	13
CS16166	16.00	16.00	6.00	13.00	15.00	1.50	0.50	0.28	16
CS18126	18.00	12.00	6.00	15.00	11.00	1.50	0.50	0.28	14
CS18186	18.00	18.00	6.00	15.00	17.00	1.50	0.50	0.28	19
CS24186	24.00	18.00	6.00	21.00	17.00	1.50	0.50	0.28	26
CS24246	24.00	24.00	6.00	21.00	22.50	1.50	0.75	0.44	37
CS30246	30.00	24.00	6.00	27.00	22.50	1.50	0.75	0.44	45
CS36246	36.00	24.00	6.00	33.00	22.50	1.50	0.75	0.44	57
CS36366	36.00	36.00	6.00	33.00	34.50	1.50	0.75	0.44	70
CS12128	12.00	12.00	8.00	9.00	11.00	1.50	0.50	0.28	12
CS16168	16.00	16.00	8.00	13.00	15.00	1.50	0.50	0.28	18
CS18188	18.00	18.00	8.00	15.00	17.00	1.50	0.50	0.28	21
CS24248	24.00	24.00	8.00	21.00	22.50	1.50	0.75	0.44	42
CS36248	36.00	24.00	8.00	33.00	22.50	1.50	0.75	0.44	65
CS202010	20.00	20.00	10.00	17.00	19.00	1.50	0.75	0.44	35
CS242410	24.00	24.00	10.00	21.00	22.50	1.50	0.50	0.28	49
CS302010	30.00	20.00	10.00	27.00	18.50	1.50	0.75	0.44	55
CS362410	36.00	24.00	10.00	33.00	22.50	1.50	0.75	0.44	70
CS363612	36.00	36.00	12.00	33.00	34.50	1.50	0.75	0.44	88

Data subject to change without notice

