



## Liquidtight Flexible Metal Conduit Fittings T&B Catalog Number:

5335SST  
**UPC Number:** 78621097765  
**Status:** Active  
**Description:**

1-1/4 in. straight stainless steel liquidtight connector.

### Features

Available in straight, 45 degree and 90 degree angled configurations to fit conduit from 3/8 in. to 2 in.

### Application

Ideal for industrial MRO and OEM applications in food and beverage, pharmaceutical, petrochemical, wastewater, salt water and other corrosive environments.

Stronger and more UV-resistant than non-metallic fittings.

Rated for temperatures up to 105 degrees C (221 degree F)

Connects metallic-cored liquidtight conduit to a box or enclosure

### General

Trade Size (inches)	1 1/4
Material	Stainless Steel
Working Temperatures	Up to 105 degree C (221 degree F)

### Dimension Information

Dimension A (inches)	1.72
Dimension B (inches)	2.12

### Specifications

3dmodel Available on Website

### Packaging

T&B Inner Pack	5
Package in Units	20
T&B Sold in UOM	Each
T&B Weight Per UOM	61.5 lbs. per 100

### Application Support

304 Stainless Steel Corrosion Compatibility Chart Available on Website

T&B Sales Drawings wsd-000171

### Certifications

RoHS Compliance Yes

**Certifications**

File Nbr:  
E 23018

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:[techsupport@tnb.com](mailto:techsupport@tnb.com)