









THIS DRAWING IS A CONTROLLED DOCUMENT.

USED ON										
TOOL NUMBER  -1 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 		CONTACT DESCRIPTION	APPLIC. SPECIF.
							LOOSE PIECE 	STRIP FORM 		
91501-1 91501-3	0.2 - 0.38 [24-22] 0.5-0.6 [20]	1.52 MAX [.060 MAX]	YES	NO	3.18 ± 0.38 [.125 ± .015]	0.74 ± 0.05 [.029 ± .002] 0.89 ± 0.05 [.035 ± .002]	794610-[]	794606-[]	Micro MATE-N-LOK Contacts	114-13000
91502-1 91502-3	0.05-0.15 [26-30]	1.52 MAX [.060 MAX]	YES	NO	3.81 ± 0.38 [.150 ± .015]	0.58 ± .05 [.023 ± .002]	794611-[]	794607-[]	Micro MATE-N-LOK Contacts	114-13000
91504-1 91504-3	0.5 - 2.1 [20-14] (Two Wires Total) 0.8-0.9[18] plus (+) 0.8-1.4[18-16]	2.54 - 3.3 [.100-.130] 2.92 MAX [.115 MAX]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.35 ± 0.05 [.053 ± .002] 1.63 ± 0.08 [.064 ± .003]	60619-[] 60620-[] 170121-[] 350638-[] 350639-[]	61117-[] 61118-[] 170120-[] 350557-[] 350558-[] 917636-1	Commercial MATE-N-LOK contacts	114-1012
91512-1 91512-3	0.20 - 0.56 [24-20] 0.75 - 0.96 [18]	1.52 - 2.54 [.060-.100]	YES	NO	4.75 ± 0.38 [.187 ± .015]	0.99 ± 0.05 [.039 ± .002] 1.24 ± 0.05 [.049 ± .002]	61473-[] 60618-[] 60617-[] 170148-[]	61115-[] 61116-[] 61314-[] 170147-[]	Commercial MATE-N-LOK contacts	114-1012
91528-1 91528-3	0.2 - 0.6 [24-20] 0.8 - 0.9 [18]	1.09-1.91 [.043-.075] 1.52-2.54 [.060-.100\]	YES	NO	4.75 ± 0.38 [.187 ± .015]	0.99 ± 0.05 [.039 ± .002] 1.24 ± 0.05 [.049 ± .002]	61473-[] 60618-[] 60617-[]	61115-[] 61116-[] 61314-[]	Commercial MATE-N-LOK contacts	114-1012
91597-1 91597-3	0.20 - 0.56 [24-20] 0.75 - 0.89 [18]	1.52 - 2.54 [.060-.100]	YES	NO	4.75 ± 0.38 [.187 ± .015]	0.99 ± 0.05 [.039 ± .002] 1.24 ± 0.05 [.049 ± .002]	640706-[] 640707-[] 770258-[] 770522-[]	640252-[] 350980-[] 770476-[]	SL-156 receptacles BIFURCATED LEAF CONTACT	114-1021 114-1015
91598-1 91598-3	0.2 - 0.6 [24-20] 0.8 - 0.9 [18]	1.09-1.91 [.043-.075] 1.52-2.54 [.060-.100\]	YES	NO	4.75 ± 0.38 [.187 ± .015]	0.99 ± 0.05 [.039 ± .002] 1.24 ± 0.05 [.049 ± .002]	640706-[] 640707-[] 770258-[] 770522-[]	640252-[] 350980-[] 770476-[]	SL-156 receptacles BIFURCATED LEAF CONTACT	114-1021 114-1015

① LIST OF APPLIED CONTACT PART NUMBERS
IS SUBJECT TO CHANGE. FOR CURRENT
INFORMATION, CONTACT THE TOOLING
ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and MATE-N-LOK are trademarks.

③ -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

LOC
A
DIST
00

	B5	REVISED		10/2016	AW	CM
P	LTR	REVISION RECORD		DATE	DWN	APVD

DIMENSIONS: mm	TOLERANCES, UNLESS OTHERWISE SPECIFIED:	
	0 PLC	± —
	1 PLC	± —
	2 PLC	± —
	3 PLC	± —
	4 PLC	± —

DWN	21FEB2012	MATERIAL	HEAT TREAT		
M.YOUNGER		-	-		
CHK	22FEB2012	-	-		
B.A. WOLFE		 TE Connectivity			
APVD	22FEB2012				
B.A. WOLFE					
NAME					
CERTI-CRIMP II TOOL DATA SHEET MATE-N-LOK CONTACT FAMILY					
SCALE	SIZE	DRAWING NO	SHEET	REV	
-	A1	1583001	1	or 1	B5