

EvoMaxx XL

Multifunktions Seitenschneider, C60

Multifunctional HD Diagonal Cutter, C60

technische Daten:

technical specifications:

mm		Ø mm			g
mm	"	MH	H	P	
180	7	3,5	2,5	2,0	270



Abisolieren
Stripping
1,5 + 2,5 mm²



Aderendhülsen crümpen
Crimping of ferrules
1,5 - 2,5mm²



Abschneiden von Messingschrauben
Plain shearing of brass screws
M 3,5 + M 4



Ösen biegen
Looping device
Ø 4, 5, 6 mm



Flachschneider
Accurate flat cutter



Seitenschneider
Diagonal cutter
14 mm length

EvoTel

KraftTelefonzange, C60

HD Long Nose Pliers, C 60



technische Daten:
technical specifications:

		Ø mm			
mm	"	MH	H	P	g
220	9	3,0	2,0	1,4	295





Aderendhülsenzange für Aderendhülsen DIN 46 228

Spezifikationen							DIN ISO 5743	
Artikel- nummer	2022							g
				mm	"			
49-140	•			145	5 7/8	0,25-2,5mm ²	130	
49-180	•			180	7	0,25-16mm ²	250	



Crimping pliers for cable terminals according to DIN 46 228

Specification							DIN ISO 5743	
Ref. No.	2022							g
				mm	"			
49-140	•			145	5 7/8	0,25-2,5mm ²	130	
49-180	•			180	7	0,25-16mm ²	250	





Aderendhülsen-Set

bestehend aus Artikel 49-180 und
Spannungsprüfer, je 100 Stück isolierten
Aderendhülsen 0,5; 0,75; 1,5; 2,5mm²
sowie 50 Stück 4mm²

Spezifikationen						DIN ISO 5743	
Artikel- nummer	2022					g	
						mm	"
76-330	•					0,25-16mm ²	700



Crimp assortment

consists of item 49-180, voltage tester
and cable terminals 0,5; 0,75; 1,5;
2,5mm² à 100 pcs. and 50 pcs. 4mm²

Specification						DIN ISO 5743	
Ref. No.	2022					g	
						mm	"
76-330	•					0,25-16mm ²	700





Wasserpumpenzange - Klassisches Modell mit durchgestecktem Gelenk (6- bzw. 7-fach Raste)

Spezifikationen										DIN ISO 8976	
Artikel- nummer	2600	2622	2700							g	
77-170	•	•	•							145	160
77-250	•	•	•							275	290
77-300	•	•	•							465	480



Waterpump pliers - Classic with box joint (6 or 7 postions)

Specification										DIN ISO 8976	
Ref. No.	2600	2622	2700							g	
77-170	•	•	•							145	160
77-250	•	•	•							275	290
77-300	•	•	•							465	480

