

Home: Crimp Housings >

Part Number: 49502-0700

1.25mm Pitch Wire-to-Board Female Housing, Vertical, Use With 49706 Crimp Terminal, 7 Circuits

Status: OBSOLETE

Replacement: Contact Molex

Series: 49502

Category: Crimp Housings

Go to **Part Detail**▼

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)

[Email this page](#)

Series image - Reference only

Mates With Part(s):
[53047](#), [53048](#), [53261](#), [53398](#)

Use With Part(s):
[49706](#)

Product Environmental Compliance

EU ELV:Product not active

EU RoHS:Product not active

EU RoHS Phthalates:Product not active

China RoHS:

REACH SVHC:Product not active

Low-Halogen Status:Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements
EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C
*IPC 1752A Class D
*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? EmailProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

COLLAPSE ALL

▼ General

Status	Obsolete
Category	Crimp Housings
Series	49502
Application	Signal
Product Name	N/A
UPC	822348137411

▼ Physical

Circuits (maximum)	7
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Compliant	No
Material - Resin	Polyester
Net Weight	0.063/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Stackable	No
Temperature Range - Operating	-40°C to +85°C