



(0,635mm) .025"

QMS-RA-PC, QFS-RA-PC SERIES

QFS-052-01-SL-D-RA-PC4

QMS-052-01-SL-D-RA-PC4

HIGH SPEED SIGNAL WITH POWER

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?QMS-RA-PC or www.samtec.com?QFS-RA-PC

Insulator Material:
Liquid Crystal Polymer

Terminal & Ground Plane Material:

Phosphor Bronze

Plating:

Au over 50µ" (1,27µm) Ni
(Tin on Ground Plane Tail and Signal Tails)

Current Rating:

Power Contact: 4.1A @ 80°C

Ground Plane: 8.9A @ 80°C

Signal Contact: 1.8A @ 80°C

Voltage Rating:

300 VAC

Operating Temp:

-55°C to +125°C

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10mm) .004" max (026-052)

(0,15mm) .006" max (078)


Board Stacking:

For applications

requiring more than two


connectors per board,

contact ipg@samtec.com



• Integral guide post


QMS	NO. OF POSITIONS	01	PLATING OPTION	D	RA	PC4	OTHER OPTION
Mates with: QFS-PC	-026, -052, -078 (Per Row)		-SL = 10µ" (0,25µm) Gold on Signal Pins and Ground Plane, Matte Tin on tails				-K = Polyimide film Pick & Place Pad




APPLICATION SPECIFIC OPTION

- 8 Power Pins/End.
 - -02 lead style for (2,36mm) .093" thick board
- Call Samtec.

QFS	NO. OF POSITIONS	01	PLATING OPTION	D	RA	PC4	OTHER OPTION
Mates with: QMS-PC	-026, -052, -078 (Per Row)		-SL = 10µ" (0,25µm) Gold on Signal Pins and Ground Plane, Matte Tin on tails				-K = Polyimide film Pick & Place Pad



APPLICATION



Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
 SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292 SAMTEC ISRAEL • Tel: 972-3-7526600
 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-61103766 SAMTEC TAIWAN • Tel: 886-2-2735-6109
 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9512 7747 SAMTEC SOUTH AFRICA • Tel: 27 11 452 8112