

# D/MS Accessories

## D/MS Series



### D/MS Series of Cable Clamps and Back Shells




### Cable Clamp (With Rubber Bushing)

#### D/MS3057- □ □ A

Material/Finish

.....Aluminum alloy/Zinc Plating, Trivalent chromate finish (Black)




| P/N          | Shell Size | A     | B     | C Thread       | D     | E    | F     | G     | Bushing Part Number |
|--------------|------------|-------|-------|----------------|-------|------|-------|-------|---------------------|
| D/MS3057-4A  | 10SL, 12S  | 20.62 | 10.31 | 5/8-24 UNEF    | 22.23 | 69.8 | 5.59  | 7.67  | AN3420-4            |
| D/MS3057-6A  | 14S        | 22.23 | 10.31 | 3/4-20 UNEF    | 26.97 | 66.7 | 7.92  | 10.85 | AN3420-6            |
| D/MS3057-8A  | 16S, 16    | 23.83 | 10.31 | 7/8-20 UNEF    | 29.36 | 63.5 | 11.10 | 14.02 | AN3420-8            |
| D/MS3057-10A | 18         | 23.83 | 10.31 | 1-20 UNEF      | 31.75 | 60.3 | 14.27 | 15.62 | AN3420-10           |
| D/MS3057-12A | 20, 22     | 23.83 | 10.31 | 1 3/16-18 UNEF | 37.31 | 57.2 | 15.88 | 18.80 | AN3420-12           |
| D/MS3057-16A | 24, 28     | 26.19 | 10.31 | 1 7/16-18 UNEF | 42.88 | 54.0 | 19.05 | 23.55 | AN3420-16           |
| D/MS3057-20A | 32         | 27.79 | 11.91 | 1 3/4-18 UNS   | 51.59 | 50.8 | 23.80 | 31.50 | AN3420-20           |
| D/MS3057-24A | 36         | 29.36 | 13.49 | 2-18 UNS       | 57.94 | 47.6 | 31.75 | 34.67 | AN3420-24           |

### Cable Clamp (Less Rubber Bushing)

#### D/MS3057A- □ □

Material/Finish

.....Aluminum alloy/Zinc Plating, Trivalent chromate finish (Black)



| P/N          | Shell Size | A     | B     | C Thread       | D     |
|--------------|------------|-------|-------|----------------|-------|
| D/MS3057A-4  | 10SL, 12S  | 20.62 | 10.31 | 5/8-24 UNEF    | 22.23 |
| D/MS3057A-6  | 14S        | 22.23 | 10.31 | 3/4-20 UNEF    | 26.97 |
| D/MS3057A-8  | 16S, 16    | 23.83 | 10.31 | 7/8-20 UNEF    | 29.36 |
| D/MS3057A-10 | 18         | 23.83 | 10.31 | 1-20 UNEF      | 31.75 |
| D/MS3057A-12 | 20, 22     | 23.83 | 10.31 | 1 3/16-18 UNEF | 37.31 |
| D/MS3057A-16 | 24, 28     | 26.19 | 10.31 | 1 7/16-18 UNEF | 42.88 |
| D/MS3057A-20 | 32         | 27.79 | 11.91 | 1 3/4-18 UNS   | 51.59 |
| D/MS3057A-24 | 36         | 29.36 | 13.49 | 2-18 UNS       | 57.94 |


Specifications are subject to change without notice for purpose of product modification.

<http://www.ddknet.co.jp>

## ▶ Rubber Bushings

### AN3420- □ □


| P/N       | A    | B     | C     | D    | E   |
|-----------|------|-------|-------|------|-----|
| AN3420-4  | 69.8 | 5.59  | 7.67  | 14.5 | 2.3 |
| AN3420-6  | 66.7 | 7.92  | 10.85 | 17.5 | 2.3 |
| AN3420-8  | 63.5 | 11.10 | 14.02 | 20.8 | 2.3 |
| AN3420-10 | 60.3 | 14.27 | 15.62 | 23.7 | 2.3 |
| AN3420-12 | 57.2 | 15.88 | 18.80 | 28.2 | 2.3 |
| AN3420-16 | 54.0 | 19.05 | 23.55 | 35.0 | 2.9 |
| AN3420-20 | 50.8 | 23.80 | 31.50 | 42.8 | 2.9 |
| AN3420-24 | 47.6 | 31.75 | 34.67 | 48.8 | 2.9 |



## ▶ Environmental Bushings

### CE3420- □ □ - □

| P/N         | A    | B    | C    | D    | E   | Applicable Cable Dia.<br>(Reference, Only) |
|-------------|------|------|------|------|-----|--------------------------------------------|
| CE3420-4-1  | 5.6  | 12.9 | 7.5  | 38.3 | 6.4 | 3.6 - 5.6                                  |
| CE3420-6-1  | 9.0  | 15.7 | 10.9 | 36.4 | 6.7 | 7.0 - 9.0                                  |
| CE3420-8-1  | 12.0 | 19.1 | 14.0 | 37.5 | 6.5 | 9.5 - 12.0                                 |
| CE3420-8-2  | 10.5 |      |      |      |     | 8.0 - 10.5                                 |
| CE3420-10-1 | 14.1 |      |      |      |     | 10.5 - 14.1                                |
| CE3420-10-2 | 11.0 | 22.2 | 15.5 | 38.5 | 7.5 | 8.5 - 11.0                                 |
| CE3420-10-3 | 8.7  |      |      |      |     | 6.5 - 8.7                                  |
| CE3420-12-1 | 16.0 |      |      |      |     | 12.5 - 16.0                                |
| CE3420-12-2 | 13.0 | 26.9 | 18.6 | 39.3 | 8.3 | 9.5 - 13.0                                 |
| CE3420-12-3 | 10.0 |      |      |      |     | 6.8 - 10.0                                 |
| CE3420-12-7 | 17.0 |      |      |      |     | 15.0 - 17.0                                |
| CE3420-16-1 | 19.1 |      |      |      |     | 15.0 - 19.1                                |
| CE3420-16-2 | 15.5 | 33.2 | 23.4 | 40.0 | 8.9 | 13.0 - 15.5                                |
| CE3420-16-6 | 20.0 |      |      |      |     | 18.5 - 20.0                                |
| CE3420-20-1 | 23.8 | 40.5 | 31.3 | 41.0 | 9.5 | 22.0 - 23.8                                |
| CE3420-20-2 | 26.6 |      |      |      | 8.7 | 24.0 - 26.6                                |




## ▶ Adapters

### D/MS3055- □ □ - □

Material/Finish

.....Aluminum alloy/Zinc Plating, Trivalent chromate finish (Black)



| P/N               | A Thread              | B Thread              | C  | D    | E  |
|-------------------|-----------------------|-----------------------|----|------|----|
| D/MS3055-18-8- □  | 1 - 20 UNEF - 2B      | 7/8 - 20 UNEF - 2A    | 30 | 20.4 | 12 |
| D/MS3055-18-10- □ | 1 - 20 UNEF - 2B      | 7/8-20 UNEF - 2A      | 30 | 22.4 | 12 |
| D/MS3055-22-8- □  | 1 3/16 - 18 UNEF - 2B | 7/8 - 20 UNEF - 2A    | 35 | 22.2 | 12 |
| D/MS3055-22-8L- □ | 1 3/16 - 18 UNEF - 2B | 7/8 - 20 UNEF - 2A    | 35 | 28.5 | 12 |
| D/MS3055-22-12- □ | 1 3/16 - 18 UNEF - 2B | 1 3/16 - 18 UNEF-2A   | 35 | 22.3 | 12 |
| D/MS3055-28-16- □ | 1 7/16 - 18 UNEF - 2B | 1 7/16 - 18 UNEF - 2A | 41 | 22.4 | 12 |

Specifications are subject to change without notice for purpose of product modification.


## ▶ CAP and Chain Assembly

### D/MS25042- □□ DK

Material/Finish

.....Copper alloy/Zinc Plating, Trivalent chromate finish (Black)

| P/N            | Shell Size | Threads A    | B     | C     | D   | E      |
|----------------|------------|--------------|-------|-------|-----|--------|
| D/MS25042-10DK | 10SL       | 5/8-24UNEF   | 16.66 | 17.45 | 3.8 | 170.78 |
| D/MS25042-12DK | 12S        | 3/4-20UNEF   | 21.44 | 20.62 | 3.8 | 170.78 |
| D/MS25042-14DK | 14S        | 7/8-20UNEF   | 21.44 | 23.80 | 3.8 | 170.78 |
| D/MS25042-16DK | 16S,16     | 1-20UNEF     | 21.44 | 26.97 | 3.8 | 170.78 |
| D/MS25042-18DK | 18         | 1 1/8-18UNEF | 21.44 | 30.15 | 3.8 | 170.78 |
| D/MS25042-20DK | 20         | 1 1/4-18UNEF | 21.44 | 33.32 | 4.6 | 170.78 |
| D/MS25042-22DK | 22         | 1 3/8-18UNEF | 21.44 | 36.50 | 4.6 | 170.78 |
| D/MS25042-24DK | 24         | 1 1/2-18UNEF | 21.44 | 39.67 | 4.6 | 170.78 |
| D/MS25042-28DK | 28         | 1 3/4-18UNS  | 21.44 | 46.02 | 4.6 | 170.78 |
| D/MS25042-32DK | 32         | 2-18UNS      | 21.44 | 52.37 | 5.8 | 170.78 |
| D/MS25042-36DK | 36         | 2 1/4-16UN   | 21.44 | 58.72 | 5.8 | 170.78 |



### D/MS25043- □□ DK

Material/Finish

.....Copper alloy/Zinc Plating, Trivalent chromate finish (Black)

| P/N            | Shell Size | Threads A    | B     | C     | D   | E      |
|----------------|------------|--------------|-------|-------|-----|--------|
| D/MS25043-10DK | 10SL       | 5/8-24UNEF   | 11.91 | 20.70 | 3.8 | 170.78 |
| D/MS25043-12DK | 12S        | 3/4-20UNEF   | 11.91 | 25.40 | 3.8 | 170.78 |
| D/MS25043-14DK | 14S        | 7/8-20UNEF   | 11.91 | 28.58 | 3.8 | 170.78 |
| D/MS25043-16DK | 16S,16     | 1-20UNEF     | 11.91 | 30.18 | 3.8 | 170.78 |
| D/MS25043-18DK | 18         | 1 1/8-18UNEF | 11.91 | 34.13 | 3.8 | 170.78 |
| D/MS25043-20DK | 20         | 1 1/4-18UNEF | 11.91 | 37.31 | 3.8 | 170.78 |
| D/MS25043-22DK | 22         | 1 3/8-18UNEF | 11.91 | 40.49 | 3.8 | 170.78 |
| D/MS25043-24DK | 24         | 1 1/2-18UNEF | 11.91 | 43.66 | 4.6 | 170.78 |
| D/MS25043-28DK | 28         | 1 3/4-18UNS  | 13.49 | 50.01 | 4.6 | 170.78 |
| D/MS25043-32DK | 32         | 2-18UNS      | 13.49 | 56.36 | 4.6 | 170.78 |
| D/MS25043-36DK | 36         | 2 1/4-16UN   | 13.49 | 62.71 | 4.6 | 170.78 |

