



## Pressure switches for mounting on plan 25x32 Positive output Part number 81505150




■ XXX

|          | Type            | Setting range |
|----------|-----------------|---------------|
| 81505140 | Positive output | 50 →500 mb    |
| 81505150 | Positive output | 0,1 →2,5 b    |
| 81505160 | Positive output | 2 →8 b        |
| 81502140 | Negative output | 50 →500 mb    |
| 81502150 | Negative output | 0,1 →2,5 b    |
| 81502160 | Negative output | 2 →8 b        |


### Symbol

|                              |                   |
|------------------------------|-------------------|
| Orifice diameter mm          | 2,5               |
| Flow at 4 bars NI/min        | 170               |
| Hysteresis 50→500 mb         | 60 mb             |
| Hysteresis 0,1→2,5 b         | 100 mb            |
| Hysteresis 2→8 b             | 320 mb            |
| Connection - Sub-base        | ■                 |
| Operating temperature (° C)  | -5 + 50           |
| Mechanical life (operations) | 3.10 <sup>6</sup> |
| Weight (g)                   | 160               |
| Accuracy 0,1→2,5 mb          | 10%               |
| Accuracy 2→8 b               | 4%                |
| Accuracy 50→500 mb           | 4%                |

### Dimension Diagram : \*\*\* TRADUCTION MANQUANTE \*\*\*




### : \*\*\* TRADUCTION MANQUANTE \*\*\*



\*\*\* TRADUCTION MANQUANTE \*\*\*

| N° | Legend |
|----|--------|
|----|--------|

### Curves : \*\*\* TRADUCTION MANQUANTE \*\*\*



| N° | Legend |
|----|--------|
|----|--------|

|   |  |
|---|--|
| 1 |  |
| 2 |  |
| 3 |  |
| 4 |  |
| 5 |  |

: \*\*\* TRADUCTION MANQUANTE \*\*\*

