



## Datasheet for part number DE9PV

|                                  |                         |                     |                    |
|----------------------------------|-------------------------|---------------------|--------------------|
| Our Catalog Part Number: DE-9P-V |                         |                     |                    |
| Brand: Cannon                    | Product Category: D Sub | Product Line: D Sub | Series: ORIGINAL D |

| Product Datasheet               |                                                             |
|---------------------------------|-------------------------------------------------------------|
| General                         | Standard D-Subminiature                                     |
| Wire Gauge Range AWG            | AWG 20-28                                                   |
| Mating Cycles                   | 50                                                          |
| Dielectric Withstanding Voltage | 1200 VAC at sea level                                       |
| Current Rating                  | 7.5 A at 85°C / 5 A at 105°C                                |
| Contact Resistance              | 10 milli Ohm max                                            |
| Operating Temperature           | -55°/+125°                                                  |
| Salt Spray Test                 | 20 hours                                                    |
| Shell Material                  | steel                                                       |
| Shell Finish                    | yellow chromate over cadmium or zinc                        |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                            |
| Insulator Color                 | black                                                       |
| Contact Arrangement             | 9 contacts size 20                                          |
| Gender                          | Pin                                                         |
| Contact Type                    | turned                                                      |
| Contact Material                | copper alloy                                                |
| Contact Finish                  | gold flash (Performance Class 3)                            |
| Contact Termination             | Solder Pot                                                  |
| Mounting Methode                | Plastic bracket with grounding brackets with M3 Captive Nut |