

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301080151

Status:

Active

Overview:

Wide-Area Lighting Products

Description:

Super-Safeway Twin Tube 30W Fluorescent Work Light, Cord Type 16/3 SJOW 7.62m (25.0') Cord Length

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E174254

General

Product Family

Series

NEMA Configuration

Outlet

Overview

Product Name

Type

UPC

Portable Lighting

130108

NEMA 5-15

None

Wide-Area Lighting Products

Super-Safeway

Wide Area Lamps

78678867260

Physical

Cord Length - Primary

Cord Length - Secondary

Depth

Duty

Guard Included

Guard Type

Height

Length

Material - Guard

Mounting Style

Packaging Type

Socket Construction

7.62m (25.0')

N/A

190.75mm (7.510")

Industrial

Yes

Clear Butyrate

82.55mm (3.250")

625.35mm (24.620")

Butyrate

Straps

Carton

N/A

Electrical

Bulb Type

Cord Type - Primary

Lamp Type

Lamp Wattage - Maximum

Lumens

On/Off Switch

Voltage (Fixture) - Maximum

Fluorescent

16/3 SJOW

F15/T8

30W

1820

No

120VAC 60 HZ

Material Info

Engineering Number

1324



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130108 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION