




Isolierkörpermaterial

Nylon 9T, UL94V-0

Kontaktmaterial

Phosphorbronze

Kontaktoberfläche

Ni, Sn

Kontaktwiderstand

15mΩ max

Isolationswiderstand

10000MΩ min

Strombelastbarkeit

1A

Betriebstemperatur

-40°C - +105°C

Betriebsspannung

100V AC

Prüfspannung

500V AC

Verpackung

Stangenverpackung

Insulator material

Nylon 9T, UL94V-0

Contact material

Phosphor bronze

Plating

Ni, Sn

Contact resistance

15mΩ max

Insulation resistance

10000MΩ min

Current rating

1A

Operating temperature

-40°C - +105°C

Operating voltage

100V AC

Test voltage




500V AC

Packing

Tube packing

Dimensions

No. of contacts	A	B	C	D	E	F
20	15.34	15.34	5.08	5.08	10.03	10.03
28	17.85	17.85	7.62	7.62	12.57	12.57
32	17.85	20.42	7.62	10.16	12.57	15.11
44	23.07	23.07	12.70	12.70	17.65	17.65
52	25.50	25.50	15.24	15.24	20.19	20.19
68	31.00	31.00	20.32	20.32	25.27	25.27
84	36.10	36.10	25.40	25.40	30.35	30.35



Bestellcode / Ordercode

Polzahl

20 / 28 / 32 / 44 / 52 / 68 / 84

Ausführung

SM - ohne Polarisierung
SM/P - mit Polarisierung

No. of contacts

20 / 28 / 32 / 44 / 52 / 68 / 84

Version

SM - without polarizing peg
SM/P - with polarizing peg

A - CCS 0 xx - Z - x

Bitte „x“ durch die geeignete Option ersetzen
Please replace „x“ appropriate option