


Rating	20A 125VAC 10A 250VAC 16A 125VAC 3/4HP  10A 277VAC 3/4HP	Mounting Hole		Circuit Diagram	
	21A 14VDC				
Contact Resistance	50m ohm Max.			SEE CHART	
Insulation Resistance	DC 500V 100M ohm Min.				
Dielectric Strength	AC 1500V 1 minute	Thickness(mm)	X(mm)		Y(mm)
Operation Temperature	-20°~+85°	0.75~1.25	21.2+0.1		36.6 ^{+0.2} ₋₀
Switch Function	SEE CHART	1.25~2.0			36.8 ^{+0.2} ₋₀
		2.0~3.0		37.0 ^{+0.2} ₋₀	



0 1  .250" SQ
0 4  SAE SQ
0 5  SO
0 8  SC 6-32UNC

() = Momentary Function



RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 1/21/11

Rev. 0

Unit: mm

Checked By: G.Guld

Title:

ROCKER SWITCH

CW P/N:

GRB260XXSERIES