samtec



(1,27mm) .050"

FTS SERIES

MICRO LOW PROFILE TERMINAL STRIPS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?FTS

HI-TEMP

Insulator Material:
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Current Rating:
1.75A @ 80°C ambient
Operating Temp Range:
-55°C to +125°C
Plating:
Sn or Au over 50µ" (1,27µm) Ni
RoHS Compliant:
Yes
Lead–Free Solderable:
Yes
SMT Lead Coplanarity:
.004" (0,10mm) max

Mates with:
FFSD, CLP, FLE, SFMC (LIF)

OPTIONS





ALSO AVAILABLE

Single row (Mates to CLP Series). Call Samtec.

APPLICATION SPECIFIC OPTION

Alignment Pin. Call Samtec.

FTS – 1 – NO. PINS PER ROW – LEAD STYLE – PLATING OPTION – ROW OPTION – OTHER OPTION

NO. PINS PER ROW
02 thru 50
(except –S & –SA option = 05 thru 46)

LEAD STYLE

–01
= .120" (3,05mm) Post (Mates with FFSD)

–02
= .075" (1,91mm) Post (Mates with FLE)

–03
= .065" (1,65mm) Post (Mates with CLP)

PLATING OPTION

–F
= Gold flash on post, Matte Tin on tail

–L
= 10µ" (0,25µm) Gold on post, Matte Tin on tail

ROW OPTION

–DV
= Double Vertical SMT

–D
= Double Row Through-hole

LEAD STYLE	A
–01	(3,05) .120
–02	(1,91) .075
–03	(1,65) .065

OTHER OPTION

–SA
= End Shroud with Alignment Pin (05 thru 46 positions. Style -02 & -03 only)

–S
= End Shroud (05 thru 46 positions. Style -02 & -03 only)

–P
= Pick & Place Pad (05 positions minimum)

–TR
= Tape & Reel (-DV only)



Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683