

Glass

POWER	400 mW	400 mW	500 mW	1.5 W
PACKAGE	DO-7		DO-35	DO-41
Zener Volts				
27		1N971 B	BZX79C27	1N5935 B
28				
30		1N972 B	BZX79C30	1N5936 B
33		1N973 B	BZX79C33	1N5937 B
36		1N974 B	BZX79C36	1N5938 B
39		1N975 B	BZX79C39	1N5939 B
43		1N976 B	BZX79C43	1N5940 B
47		1N977 B	BZX79C47	1N5941 B
51		1N978 B	BZX79C51	1N5942 B
56		1N979 B	BZX79C56	1N5943 B
60				
62		1N980 B	BZX79C62	1N5944 B
68		1N981 B	BZX79C68	1N5945 B
75		1N982 B	BZX79C75	1N5946 B
82		1N983 B	BZX79C82	1N5947 B
87				
91		1N984 B	BZX79C91	1N5948 B
100		1N985 B	BZX79C100	1N5949 B
110		1N986 B	BZX79C110	1N5950 B
120		1N987 B	BZX79C120	1N5951 B
130		1N988 B	BZX79C130	1N5952 B
140				
150		1N989 B	BZX79C150	1N5953 B
160		1N990 B	BZX79C160	1N5954 B
170				
180		1N991 B	BZX79C180	1N5955 B
190				
200		1N992 B	BZX79C200	1N5956 B

Metal

Note: All the above preferred types have 50/o tolerance.

POWER	10 W	50 W				
PACKAGE	DO-4		TO-3		DO-5	
Zener Volts						
3.9	1N3993 A		1N4557 B		1N4549 B	
4.3	1N3994 A		1N4558 B		1N4550 B	
4.7	1N3995 A		1N4559 B		1N4551 B	
5.1	1N3996 A		1N4560 B		1N4552 B	
5.6	1N3997 A		1N4561 B		1N4553 B	
6.2	1N3998 A					
6.8	1N3999 A	1N2970 B	1N4563 B	1N2804 B	1N4555 B	1N3305 B
7.5	1N4000 A	1N2971 B	1N4564 B	1N2805 B	1N4556 B	1N3306 B
8.2		1N2972 B		1N2806 B		1N3307 B
9.1		1N2973 B		1N2807 B		1N3308 B
10		1N2974 B		1N2808 B		1N3309 B
11		1N2975 B		1N2809 B		1N3310 B
12		1N2976 B		1N2810 B		1N3311 B
13		1N2977 B		1N2811 B		1N3312 B
14		1N2978 B		1N2812 B		1N3313 B
15		1N2979 B		1N2813 B		1N3314 B
16		1N2980 B		1N2814 B		1N3315 B
17		1N2981 B		1N2815 B		1N3316 B
18		1N2982 B		1N2816 B		1N3317 B
19		1N2983 B		1N2817 B		1N3318 B
20		1N2984 B		1N2818 B		1N3319 B