



Sample photo

Order symbol: ABS 200/88 XHT
Product nbr: 6083930

Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074052025
El. number:
Finland 3435282
Denmark 8212023699

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:		L	W	H	Rating:
mm:		255	180	88	Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 07 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
inch:		10	7.1	3.5	
Materials:					
Material:		ABS			
Base colour:		RAL 7035			
Cover colour:		Smoked grey			
Cover screws material:		Polyamide			
Cover screws colour:		Black			
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			Fimko Europe EN 50298 1998 Gost R
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
MIV 200		Mounting plate			
MIN 15		DIN-15 Mounting rail			
MIN 20		DIN-15 Mounting rail			
MIV 15		DIN-35 Mounting rail			
MIV 20		DIN-35 Mounting rail			
FP A 200/180		Front plate			
HFP 180		Front plate hinge series			

