

Specification



IDEAL POWER
IDEAL POWER SOLUTIONS

Model Name : AC 0724A

Input Voltage	115 / 230Vac [AUTO SW.]
Input Frequency	47 ~ 63Hz
Max. In-rush Current	Cold start , 30A for 115Vac , 60A for 230Vac
Input Current	4.2A Max for 115Vac 2.1A Max for 230Vac
Output Voltage	29.2Vdc $\pm$ 0.2V (Absorption Charge) 27.4Vdc $\pm$ 0.2V (Float Charge)
Start Point of Floating	0.7A $\pm$ 0.2A
Max. Charging Current	7A
Ripple / Noise	250mVp-p
FAN Control	Fan on fast speed (Bulk / Absorption Charge) Fan on slow speed (Float Charge)
LED Indication	LED1 : RED LED $\rightarrow$ POWER ON LED2 : RED LED $\rightarrow$ CHARGING GREEN LED $\rightarrow$ FULL CHARGE
Dimensions	7.32 inch (186 mm) Length 3.46 inch (88 mm) Width 1.87 inch (47.5 mm) Height
AC Power Cord	NAMA SVT 18AWG X 3C


Ideal Power, Acorn House, Tree Beech Enterprise Park, Gunn, Barnstaple, Devon, England EX32 7NZ

Web. www.idealpower.co.uk

email. sales@idealpower.co.uk

Tel. +44 (0) 845 2603400

Fax. +44 (0) 845 2603401



Case Drawing

Body View



Front Panel



Rear Panel

