



Color-Keyed®

Splice Connector

T&B Catalog Number:

54506

UPC Number:

78621054506

Status:

Active

Description:

Copper Two-Way Splice - Short Barrel for 4 AWG, 91/24 Die Code 29
Gray

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General

Style	Two-Way Standard Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#4 AWG
Wire Size Flex	91/24 = 36.7 kcmil, 133/.0177, 49/.029
Die Color	Gray
Die Code	29

Dimension Information

A (inches)	1.00
E (inches)	.37

Specifications

Voltage Rating	600V
----------------	------

Packaging

T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	1.72 lbs. per 100

Application Support

T&B Instruction Sheets	ta00676-tb2
------------------------	-------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com