


AC Inlet

161-0711-PQA-E



AC Inlet



Dimensions: mm (in.)

| SPECIFICATIONS | |
|---|--|
| Type: | snap-in AC inlet |
| Rating: | 15A / 250 VAC |
| Insulation resistance: | 100MΩ @ 500VDC |
| Dielectric strength(between terminals): | 2000VAC for 1 minute |
| Operating temperature: | -25°C to +85°C |
| Solder temperature: | Wave Soldering: Soldering Temperature 250±5°C, duration 3~5 sec. Manual Soldering: Soldering Temperature 380±5°C, duration 2~3 sec. |
| Resistance to Heat | Withstood a temperature of 100±2°C for 1 hour |
| Resistance to Solder Heat | Soldering temperature 260±5°C, duration 2~3 sec. |
| Housing: | Nylon 66, black |
| Terminal: | tin plated copper alloy |
| RoHS Compliant | |

Date Last Revised: 09/15/08

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC- 301140

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-0711-PQA-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-0711-PQA-E](#)