



T50I0UVM4

Standard Cable Tie, 12" Long, 50lb Tensile Strength, PA66UV, Black, 1000/pkg

Article Number: 111-00470

Part Number: T50I0UVM4

Type: T50I

Base Data

Part No.	T50I0UVM4
Type	T50I
Color	Black (BK)
Features	• UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures . • Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

Product Dimensions

Min. Tensile Strength	50.0lbs / 225.0N
Length (L)	12.0" / 305.0mm
Width (W) (imperial)	0.18"
Width (W)	4.6mm
Min. Ø Bundle	0.06" / 1.5mm
Max. Ø Bundle	3.2" / 80.0mm

Material and Specifications

Material	Polyamide 6.6 UV-resistant (PA66UV)
US MILSPEC	MS3367-7-0
Flammability	UL94 V2
Material Specification	HF
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	 RoHS
Specification	UL ZODZ2.E64139
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

Logistic and Packaging

Pkg. Qty.	1000
Carton Qty.	5000
UPC	089306254843

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
 7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512