


BOTTOM MOUNT SOCKET STRIPS

(2.54 mm) .100" PITCH • BSW SERIES



BSW

Mates:

TSW, MTSW, HTSW,
MTLW, TSM, EW, ZW,
HW, DW, PHT

FEATURES

- Bottom mount socket strips accept .025" SQ terminals.
- Ideal for soldering and plugging from the same side of the board.
- For low profile connections and high temperature soldering.

SPECIFICATIONS

Insulator Material:

Black Thermoplastic

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ" (1.27 μm) Ni

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

Insertion Depth:

(3.68 mm) .145" to

(6.35 mm) .250"

plus board thickness

PROCESSING

Lead-Free Solderable:

Wave only

ALSO AVAILABLE

Contact Samtec

Other Platings

BSW	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION
------------	----------	-------------------------	-------------------	-----------------------	-------------------

02 thru 36

-04
= Standard Lead

-24
= Low Insertion Force





-L
= 10 μ" (0.25 μm)
Gold contact,
Matte Tin on tail

-G
= 20 μ" (0.51 μm)
Gold contact,
Gold Flash on tail

-T
= Matte Tin
(Not available with
Low Insertion Force)


-S
= Single Row

-D
= Double Row



ROW OPTION	Z
-S	(4.31) .170
-D	(4.32) .170

APPLICATIONS



Note:

Some lengths, styles and options are non-standard, non-returnable.