




Catamount®



NOTES:

1. MATERIAL: NYLON 6,6
2. FLAMMABILITY: UL94V-2
3. OPERATING TEMPERATURE RANGE: -40°F [-40°C] TO 185°F [85°C]
4. MINIMUM TENSILE RATING: 120 LBS [534 N]
5. MINIMUM WIRE BUNDLE: .188 [4,76]
6. MAXIMUM WIRE BUNDLE: SEE TABLE
7. INSTALLATION TOOL/SETTING: WT197/6-8 (MS90387-2) OR ERG297/5-8

CATALOG NUMBER	MAXIMUM WIRE BUNDLE	A
L-8-120-***	2.000 [50,8]	7.964 [202,29]
L-11-120-***	3.000 [76,2]	11.000 [279,4]
L-11-120FL-***	3.000 [76,2]	11.000 [279,4]
L-14-120-***	4.000 [101,6]	14.284 [362,81]
L-14-120FL-***	4.000 [101,6]	14.284 [362,81]
L-18-120-***	4.875 [123,83]	17.611 [447,32]
L-24-120-***	7.000 [177,8]	23.611 [599,72]
L-28-120-***	8.000 [203,2]	27.611 [701,32]

* = COLOR CODE- 0= BLACK (OUTDOOR) 4= YELLOW 8= GRAY 17= FLUORESCENT YELLOW
1= BROWN 5= GREEN 9= NATURAL 18= FLUORESCENT GREEN
2= RED 6= BLUE 11= FLUORESCENT PINK 20= FLUORESCENT BLUE
3= ORANGE 7= PURPLE 16= FLUORESCENT ORANGE

** = PACKAGING- C= STD PKG (100) L= STD PKG (50) Q= STD PKG (25)

CONSULT CUSTOMER SERVICE FOR PACKAGE QUANTITY AVAILABILITY

FLUORESCENT COLORS NOT "UR" OR "CE" RECOGNIZED OR LISTED

GENERAL NOTES		Thomas & Betts www.tnb.com			
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.	2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.				
REVISIONS		DESCRIPTION: 8", 11", 14", 18", 24" & 28" SERIES 120 HEAVY DUTY CABLE TIES			
-	SEE ERN (****) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: ****	ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	REV. NO:	DRAWING NO:
		FM401182 / (2006127)	1 OF 1	-	WSD-000223