

Scotch® Filament Tape 898



Technical Data

July, 2009

Product Description

Scotch® Filament Tape 898 is a high-performance transparent packaging tape reinforced along its length with continuous glass-yarn filaments, which give the tape very high tensile strength. The transparent 3M™ Scotchpro™ backing provides excellent abrasion, moisture and scuff resistance. The adhesive is an aggressive packaging adhesive specifically formulated to provide balanced performance having both high adhesion and long term holding power.

Construction	Backing	Adhesive	Reinforcement	Backing Color
	3M™ Scotchpro™ film	Pressure sensitive synthetic rubber resin	Glass yarn	Clear

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only, and should not be used for specification purposes.

	ASTM Test Method
Adhesion to Steel:	D-3330
Tensile Strength:	D-3759
Elongation at Break:	D-3759
Total Thickness:	D-3652

Features

- Meets ASTM D5330, Type II (replaces PPP-T-97E and CID A-A-1686A).
- Abrasion and moisture resistant.
- Good handling.
- High tensile strength.
- Allows printing and illustrations to be seen through the tape.
- High shear and great initial adhesion.
- Excellent aging.
- Good protection of filaments and adhesive to provide longer package life.
- Assures maximum package performance for limited outdoor use.
- Saves time through ease of dispensing and handling when used with a 3M dispenser.
- Provides advertising and warning capability when printed.
- Low unit costs by using less tape on applications where high tensile strength is one of the main requirements.
- Good holding, with minimum amount of tape, under a wide range of application conditions.
- Holds instantly with minimum rubdown.
- Boxes remain securely closed through normal warehouse time cycles.

Scotch® Filament Tape

898

Available Sizes	Available Widths	Available Lengths
	Standard Widths: .24 in. (6 mm), .35 in. (9 mm), .47 in. (12 mm), .59 in. (15 mm), .71 in. (18 mm), .94 in. (24 mm), 1.4 in. (36 mm), 1.9 in. (48 mm), and 2.8 in. (72 mm)	60 yds. (55 m)
	.47 in. (12 mm), .59 in. (15 mm), and .71 in. (18 mm)	360 yds. (330 m)
	Core Size (ID): 3 in. (76.2 mm)	

Application Techniques	An extensive line of application equipment including hand-held manual dispensers and an automatic L-Clip applicator, the 3M-Matic™ S867, is available. Application of Scotch® Filament Tape 898 is most easily accomplished at room temperature. At colder temperatures, approaching 32°F (0°C), the adhesive becomes firm. Once applied, Scotch® Tape 898 performs well throughout the normal temperature ranges typically encountered by packaged products in shipping and storage environments.
-------------------------------	--

Storage Conditions	Store behind present stock. Store in a clean, dry place. Temperature of 40-80°F (4-26°C) and 40-50% relative humidity are recommended. Rotate your stock.
---------------------------	---

Shelf Life	To obtain best performance, use this product within 18 months from date of manufacture.
-------------------	---

Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
------------------------------	--

Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.
--------------------	--

Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
---	---

Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.
--------------------------------	--

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.

3M

Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

Scotch is a registered trademark of 3M.
3M, Scotchpro and 3M-Matic are
trademarks of 3M.
Printed in U.S.A.
©3M 2009 70-0710-0226-8 (7/09)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M](#):

[898-6mmx55m](#) [898-9mmx55m](#) [898-36mmx55m](#) [898-72mmx55m](#) [898-48mmx55m](#) [898-12mmx55m-6893](#) [898-12mmx55m-6896](#) [898-18mmx55m-6894](#) [898-18mmx55m-6897](#) [898-24mmx55m-6895](#) [898-24mmx55m-6898](#) [898-48mmx55m-48x55BK](#)