

SLIDE SWITCHES



Flush Button Style



Raised Button Style

Features:

- **Single & double pole, double throw switch configuration**
- **Logic level rating available with gold plate contacts & terminals**
- **3-position center OFF with momentary or maintained switch action in any combination**
- **Dusttight to MIL-PRF-8805 Design 2**
- **Raised & flush button contours available**
- **Choice of button color**
- **FAA/PMA available (contact factory)**
- **RoHS compliant**

Standard Characteristics/Ratings:

ELECTRICAL RATINGS:

Load	Sea Level @ 28VDC or 115VAC, 60/400Hz
Resistive	5A
Inductive	3A
Lamp	1A
DWV	1050Vrms
Logic Level	10mA @ 5VDC

Electrical Life:	100,000 cycles
-------------------------	----------------

Mechanical Life: 100,000 cycles

Seal:	Dusttight per MIL-PRF-8805 Design 2
--------------	-------------------------------------

Operating Temp Range: -55°C to +85°C

Operating Force:	24 oz +/- 10 oz
-------------------------	-----------------

Return Force: 10 oz +8 oz/-3 oz to center from maintained position

Total Travel: 0.120 inches max two directions

Overtravel: 0.010 inches min

MATERIALS:

Case: Thermoplastic


Button: Thermoplastic

Terminals:	Copper with silver Gold over silver for logic level
-------------------	--

Terminal Hardware: None provided


Mounting Hardware: Hex nut and lockwasher

SL PART NUMBER CODE




NOTE: () denotes momentary action.

SL-1111 Series




COMMERCIAL & MILITARY GRADES


SL-1211 Series



SL-2111 Series



SL-2211 Series



SL-2221 Series

