

REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

RoHS

NOTES:

Insulator Material: PBT, UL

94V-0

Contact Plating: TiN, 80-100μ”

Contact Material: Brass

Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.

Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ

Min.

Operating Temp.: -40℃~+105℃

NUMBER OF POSITIONS	DIMENSIONS	
	A	B
06	2.54	18.31
08	3.81	19.58
10	5.08	20.85
12	6.35	22.12
14	7.62	23.39
16	8.89	24.66
18	10.16	25.93
20	11.42	27.20
24	13.97	29.74
26	15.24	31.01
30	17.78	33.55
34	20.32	36.09
40	24.13	39.90
50	30.48	46.25
60	36.83	52.60
64	39.37	55.14

CnC Tech,LLC





Part No.

3210-XX-002-11-99


SCALE	SHEET	UNIT
1:1	1/1	MM

DRW NO:

REV: A



P.C.B LAYOUT



UNLESS TOLERANCE	
GENERAL	ANGLE
X. ± 0.30°	X.* ± 3.0°
.X ± 0.20	.X* ± 2.0°
.XX ± 0.15	.XX* ± 1.0°
.XXX ± 0.08	.XXX ± 0.5°

DESIGN BY	CHECK BY	APPROVE BY

DRW NO: 3210-XX-002-11-99