

**Models 7106, 7107, 7108, 7109 AND 7110
XLR (M), XLR (F): 3, 4-Pin Flanged Panel Mount***Model 7106 XLR (M) 4-Pin Rectangular Flanged Mount**Model 7108 XLR (F) 3-Pin Rectangular Flanged Mount, Black**Model 7107 XLR (F) 4-Pin Rectangular Flanged Mount**Model 7109 XLR (M) 4-Pin Rectangular Flanged Mount, Black**Model 7110 XLR (F) 4-Pin Flanged Mount, Black*

Use for your audio applications
to protect contacts and absorb
vibrations.

Features

- 3 and 4 pin audio receptacles with sturdy all metal, one piece design
- Solder cup terminations
- Front mountable.
- Female receptacles have latch lock mechanism.

Materials

- Housing is diecast zinc alloy with tarnish resistant nickel plating. (Models 7108, 7109, 7110: Black nickel plating)
- Contacts 7106, 7107, and 7109 are bronze with tin finish; contact for 7108 is nickel plated brass; Contacts for 7109, 7110 are gold plated brass
- Ground tab is steel

Ordering Information

Models: 7106, 7107, 7108, 7109, 7110.

Specifications

Number of contacts	3 or 4
Contact resistance	< 5 mΩ
Dielectric strength	1500 V dc
Wire size (AWG)	For 3-pin is 14 AWG (2.5 mm ²) max. For 4-pin is 16 AWG (1.5 mm ²) max.

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.