

TURCK

Stainless Steel Front Face



Housing Style	Part Number	ID Number	Features	Sensing Range (mm)	Output
30 mm - Embeddable, eurofast® Connection, Stainless Steel Front Face 	Bi10-EM30F-AP6X-H1141	M4614537	Stainless Steel Body and Face	10	3-Wire DC PNP
30 mm - Embeddable, eurofast Connection, Stainless Steel Front Face, Teflon Coated Barrel 	Bi10-EMT30F-AP6X-H1141	M4614563	Teflon Coated, Stainless Steel Body and Face	10	3-Wire DC PNP
30 mm - Embeddable, eurofast Connection, Stainless Steel Front Face, weldguard, Teflon Coated Barrel 	Bi10-EMT30F-AP6X-H1141/S1589	M4614598	Teflon Coated, Stainless Steel Body and Face, weldguard	10	3-Wire DC PNP



Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection	Housing	Face	Power LED	Output LED	Mating Cordset	Wiring Diagram #	Wiring Diagrams
10-30 VDC	180	≤200	-25 to +80	IP 68 /IP 69K	SS	SS	N/A	YE	RKC 4T-*/S1587	1	Diagram 1
10-30 VDC	180	≤200	-25 to +80	IP 68 /IP 69K	SS/TC	SS/TC	N/A	YE	RKC 4T-*/S1587	1	
10-30 VDC	180	≤200	-25 to +80	IP 68 /IP 69K	SS/TC	SS/WG	N/A	YE	RKC 4T-*/S1587	1	

* Length in meters.