


Kit containing 10 pieces of 5243, one of each color.



MATERIALS:

Contact – Stainless steel, Type 301, ½ Hard

Spring – Stainless steel, Type 302.

Cap – Glass Filled Nylon.

Marking: “Model 5243”

Barrel – Glass filled nylon. Color: Matches color of cap.

Marking: “POMONA GRABBER®”

Finish: Contact – Gold plated per MIL-G-45204,

Type II, 30 to 50 microinches.

RATINGS:

Operating Temperature: +102° C. (+216° F) Max.

Operating Voltage: 30VAC / 60VDC Max.

Current: 0.5 Amperes

ORDERING INFORMATION: Model 5243 & 5520 Kit

Standard Colors: Available in 10 colors: -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

Ordering Example: 5243-2 Color is Red

Ordering 5520 “Kit” – contains one color each of the 5243-.*.

SIMPLIFIED ASSEMBLY PROCEDURE

1. Pull off thumb cap to expose contact connection.
2. Thread wire through thumb cap and strip 3.18 (1/8).
3. Insert stripped end through hole on contact and solder.
4. Slide thumb cap back onto contact.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA