


EDSTL130/X (5.0 mm) EDSTLZ130/X (5.08 mm)



2-24 poles, Spacing 5.0 mm or 5.08 mm

insert required no. of poles **x**

How to order see page 5



Ratings:

Rated Voltage **300 V**

250 V

Rated Current **10 A**

10 A (T55)

Rating Impulse Voltage/Dirt Level

4 kV/3

Dimensions

Spacing **5.0 mm (5.08 mm)**

PCB Hole Diameter **1.5 mm**

Materials

Insulating Material **PA**

Flammability Class **UL94 V-0**

Temperature Range **-30 °C/+105 °C**

Contact Pin **CuZn**

Color

Black

