

LKCRF19H4

Low Profile Rivet Mount .938"X.47"-PA66, NA, Mnt Hole .25", Max Pan .134", T18-T50 Ties, 500/pk

Article Number: 151-27009

Part Number: LKCRF19H4

Type: LKCRF1



[Find a Distributor](#)

[Order Samples](#)

[Get Technical Drawings](#)

Share

Base Data

Part No.	LKCRF19H4
Type	LKCRF1
Color	Natural (NA)
Features	The low profile rivet mount accomodates the T18 through T50 series cable ties.
Application Method	Fastens with the drive rivet through a predrilled hole.
Typical Application	This mount is ideal for use in applications where space is limited and is designed to secure wiring bundles.

Product Dimensions

Length (L)	.938" / 24.0mm
Width (W) (imperial)	.470"
Width (W)	12.0mm
Max. Cable Tie Width	4.8mm
Height (H)	.157" / 4.0mm
Max. Panel Thickness	.134" / 3.40mm
Mounting Hole Ø	.250" / 6.4mm

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Specification	RoHS
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	500
Carton Qty.	4000
EAN code	5022660310560