

tyco**Electronics**

a vital part of your world

[Products](#)
[Catalog](#)
[Brands](#)
[Industries](#)
[Commerce](#)
[Supplier](#)
[Contact Us](#)
[About](#)
[Home](#)
[English](#)
[日本語](#)
Search by: **Text** | [Part Number](#)[Tips](#) ▶

Text Search:

Wednesday, 1 February, 2006

CATALOG

➔ Cross Reference

[Competitive Products](#)[Military Spec P/Ns](#)[Tyco Brand P/Ns](#)➔ [Part Number Search](#)➔ [Document Search](#)➔ [Product Type Search](#)➔ [Product Family Search](#)➔ [Alphabetical Search](#)➔ [RoHS/ELV Compliance &](#)[Alternates](#)➔ [CAD Model Search](#)➔ [Brand Search](#)➔ [Tool Search](#)➔ [Multiple Part Comparison](#)➔ [Lead Free Solutions](#)➔ [Help/Glossary](#)[Home](#)
 e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Sockets

➔ SIP Sockets

AMP**510-AG90D-20** ✓ Active
Directive 2002/95/EC
Compliant
RoHS Compliant**(Corporate P/N: 3-1437530-5)**[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
✦ General Info ✦ Sales Info ✦ Assembly Subcontractors	✦ Pricing & Availability	✦ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)**Searchable Features:**

Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Wave solder capable to 240°C, Wave solder capable to 265°C
Number of Positions:	20
Contact Style:	Screw Machine
Leg Style:	Standard
Contact Material:	Beryllium Copper
Contact Mating Area Plating:	Gold
Termination Post Length (mm [in]):	3.18 [0.125]
Sleeve Material:	Brass

Other Properties:

RoHS/ELV Compliance History:	Always was RoHS compliant
Product Series:	500 Series
Sleeve Plating:	Gold
Housing Material:	Thermoplastic Polyester
Housing Flammability Rating:	UL 94V-0
Height Above PC Board (mm [in]):	4.57 [0.180]
Centerline (mm [in]):	2.54 [0.100]
Number of Rows:	1
Breakaway Header:	Yes
Comment:	Premium Series

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]