

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [1301370100](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-15 Duplex Receptacles, Cord Clamp, Duplex Cover Plates, 0.305m (1.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
UL E38085

**General**

Product Family Power Distribution  
Series [130137](#)  
Enclosure Rating N/A  
GFCI Reset N/A  
Mounting Style Portable  
Open Neutral Relay N/A  
Overview [Watertite Wet-Location Wiring Solutions](#)  
Product Name Super-Safeway  
Receptacle Type Duplex  
Type Multiple Outlet Box  
UPC 78678879620

**Physical**

Cord Diameter 13.59mm (.535")  
Cord Grip Body Size Double C-Clamp  
Cord Length 0.305m (1.0')  
Feed-Thru No  
Flip Lid No  
Material - Housing Rubber  
Number of Receptacles 2  
Packaging Type Carton

**Electrical**

Cord Type 14/3 SOOW  
Current - Maximum per Contact 15.0A  
GFCI No  
Ground Continuity Monitor No  
NEMA Configuration NEMA 5-15  
Voltage - Maximum 125V

**Material Info**

Engineering Number 3000-1E143



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

**China RoHS**

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130137 Series](#)