






STANDARD SILVER CONTACTS		GOLD PLATED CONTACTS		NEWHOUSE/FREEPORT APPROVAL	
ELECTRICAL RATING		ELECTRICAL RATING		ENVIRONMENTAL	
AC A300 AC15 U _e I _e VOLTS AMPS 120 6 240 3		DC Q300 DC13 U _e I _e VOLTS AMPS 125 0.55 250 0.27		I _{th} = 10A IV 10μA MIN. 50V 100mA MAX.	
				IP66 NEMA 1, 4, 12, 13 TEMP RANGE : -25°C TO 85°C -13°F TO 185°F STORAGE : -40°C TO 85°C -40°F TO 185°F SHOCK : 50G PER IEC 68-2-27 VIBRATION : 10G PER IEC 68-2-6	
				  IEC 947-5-1 EN50047	
THE COPYRIGHT OF THIS DRAWING IS THE PROPERTY OF HONEYWELL LTD. THE DRAWING IS SUPPLIED IN CONFIDENCE AND MUST NOT BE USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS SUPPLIED.				THIRD ANGLE PROJECTION 	
SCALE		DIMENSIONS ARE IN		MODIFY ON CAD	
1:1		MM/INCHES.		SYSTEM ONLY	



NOTE:- CABLE AND CONNECTOR WILL BE FITTED TO BOTTOM EXIT CONDUIT ONLY. OTHER OPTIONS CUSTOMER SPECIAL'N' LISTING